THE Alfred Stieglitz COLLECTION

OBJECT RESEARCH



Alfred Stieglitz (American, 1864–1946)

The Dancing Trees

1922 Palladium print Alfred Stieglitz Collection

AIC accession number: 1949.772

Stieglitz Estate number: 23A

Inscriptions: Inscribed recto, on hinged mat, lower left, in graphite: "Treated by Steichen – 2/1950"; recto, on hinged mat, lower center, in graphite: "Alfred Stieglitz"; recto, on hinged mat, lower right, in graphite: "Dancing Trees, 1921 Palladiotype"; recto, on hinged mat, lower right, in graphite: "XRF @ AlCon 7/07 (EG)"; inscribed verso, on print, left center, in graphite: "[illegbile]"; verso, on print, center, in graphite: "[illegbile] A"; verso, on print, lower right, in graphite: "Ch 23A"; inscribed verso, on hinged mat, lower left, in graphite: "Leica / #23A"

Dimensions: 24.3 x 19.5 cm (image) 25.1 x 20.1 cm (paper)

Print thickness: 0.284 mm

Mount: Original; with original presentation window mat

X-ray fluorescence (XRF) spectrometry: See below

THE Alfred Stieglitz COLLECTION

OBJECT RESEARCH

X-RAY FLUORESCENCE (XRF) SPECTROMETRY

XRF spectral readings were taken from the recto of the work and from the mount when available. The elements listed below have been positively identified in the work; elements in bold have been attributed to the processing of the print.

Print: Fe, Pd

Mount: Ca, Ti, Cr, Mn, Fe, Zn, Sr, Pb

The graph below shows XRF spectra for three distinct measurement areas on the print: the darkest, maximum-density image area (Dmax, purple); the lightest, minimum-density image area (Dmin, green); and the mount, when available (orange). The background spectrum (gray) represents the characteristic contribution of the instrument itself as measured on a Teflon reference and is included in order to discount irrelevant elements from the print's signature. Elements were identified based on the presence of their characteristic peaks. Analysis was performed with a Bruker ARTAX air-path portable micro-XRF system equipped with a laser pointer, an integrated camera system, a Mo 12.5µm filter, and a Mo tube. Measurements were taken for 250 LT at 50 kV and 800 µA. The spectrum below illustrates the significant peaks for this print in the energy range from 2 to 15 keV.

Figure 1. (right) Locations of XRF measurements

Figure 2. (below) XRF spectra from the Dmax, Dmin, mount, and background signal produced by the analyzer.



